

# Rondish

## HushPager with Wireless ServiceCall Buttons

# NEW!

**Calls the wearer by vibrating and shows the Calling No. on a display pager and, optionally, on a Central Monitor.**

- A wireless call system to gain immediate help, typically in retail or service situations, designed to meet the worldwide need and desire to better serve, customers, patients and other service-users, without disturbance to others.
- Since it's wireless, it is much easier and faster to install than wired versions, and therefore less labor intensive and more economic. For example, calls from wireless buttons in fitting rooms are transmitted to display pagers carried by shop assistants, who receive a vibrating pager call with fitting room ID shown on the display. Service-givers are able to respond quickly and quietly giving graceful assistance without alarm sounds or flashing lights. It has potential application in many kinds of service and commercial buildings, including restaurants, hotels, shops, etc.
- Service application examples also include:
  - Medical: hospitals/elderly homes with door, bed and/or toilet monitoring etc.
  - Security: emergency/panic/door contact, with connection to a security panel.
  - Other: flooding/fire/deaf person alarm/lift fault i.e. telemetry-type applications.
- The 3 basic wireless system components are as follows:
  1. A wall-mounted Call button (WCP-02).
  2. A call/pager controller, centrally located for best coverage.
  3. A staff display HushPager with vibrator function (pendant, or belt/pocket clip options).
- Optional wireless extras are as follows:
  1. Range extenders to extend calls from the call buttons to the call/pager controller, especially \ useful in very large areas or odd-shaped, cluttered buildings.
  2. Central Monitor (CMU-02), located, for example, at the point of sale (POS) to supervise one or several groups of fitting rooms, or in the manager's office to monitor staff responsiveness. Alternatively, it can be the central station for security/medical monitoring applications.
  3. Wireless reset button (WRE-02) to reset the alarm.
  4. Wristband transmitter (TXP-01) for mobile patient call button.
  5. Bed monitor detects patient leaving a bed (See our Bed/ChairWatcher™ range of monitors with SilverLining™ pressure pads).
  6. Door monitor (DMU-02) detects patient exiting through a door. (See our DoorWatcher™ range of doors monitors).
  7. Large overhead display (LEDP-01)



(HushPager)



(WCP-02)



(Side View)



(Call/Pager Controller)



# HushPager with Wireless ServiceCall Buttons

- Call buttons have low battery alert, which is sent to the pager.
- Up to 1000 call buttons, programmed with different numbers by area, may be monitored centrally using the Central Monitor. The low battery condition of any of the alarm components is also observed from the central station, so they may be replaced.
- All units are user-programmable and easy to replace.

## Optional units



(CMU-02)



Surface - mounted  
transmitter



(TXP-01)



(WRE-02)



(LEDP-01) Size: 703mm x 110mm x 45mm



## Standard Features

- No disturbing bell, alarm sounds or flashing lights.
- HushPagers with 4-line character display.
- Automatic low battery detect with Area/ID to pager or optional Central Monitor.
- Selectable pager alerts – vibration, silent, audio or music, if sound required.
- Programmable electronic address and area/ID codes.
- Easy-to-install, without conduit or wiring.

## Specifications

- Wireless Frequencies: 315MHz (FCC) or 433MHz (EU).
- Paging System frequency bands: 132-174MHz/279-286MHz/420MHz/929-933MHz.
- Highly reliable microchip processor controls transmission of digitally encoded signals (error checking/check sum data).
- Call Button battery lifetime designed for operation in retail environment up to 7 years (dependent on number of operations).
- Pagers powered by AAA battery with typically 25 days continuous use.
- Call/Pager controller, range extenders and Central Monitor powered by AC adaptors with standby battery in case of power fail.

### NOTE:

The HushPager with Wireless ServiceCall Buttons has different country versions, primarily European and US types.

Distributed By:



Hong Kong Office:  
Rondish Company Limited  
Tel: +852 2545 2057  
Fax: +852 2541 7411  
info@rondish.com  
www.rondish.com



USA Office:  
RondishUSA LLC  
Tel: +1 858 729 0251  
Fax: +1 815 346 5396  
sales@rondishUSA.com  
www.rondishUSA.com